# F4A-PNMNR-1M

FSJ4-50B SureFlex® Jumper with interface types N Male and N Male Right Angle, 1 m

## Product Classification

Product Type	SureFlex® standard
Product Brand	HELIAX®   SureFlex®
Product Series	FSJ4-50B
General Specifications	
Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Interface, Connector A	N Male
Interface, Connector B	N Male
Specification Sheet Revision Level	А
Dimensions	
Length	1 m   3.281 ft
Nominal Size	1/2 in
Electrical Specifications	
DTF, Connector A	-32 dB
DTF, Connector B	-32 dB
VSWR/Return Loss	

Frequency Band	VSWR, typical	Return Loss, typical (dB)
0–3000 MHz	1.106	25.96
2.2–2.7 GHz	1.083	27.99

## Jumper Assembly Sample Label

Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 18, 2025

# F4A-PNMNR-1M



## **Environmental Specifications**

**Immersion Test Method** 

Meets IEC 60529:2001, IP68 in mated condition

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



#### Page 2 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 18, 2025