

H4-NMNM-60-P

HL4-50™ Jumper with interface types N Male and N Male, 60 ft



Product Classification

Product Type	Cable assembly, plenum
Product Series	HL4-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	N Male
Interface, Connector B	N Male
Specification Sheet Revision Level	A

Dimensions

Length	18.288 m 60 ft
Nominal Size	1/2 in

Electrical Specifications

3rd Order IMD Dynamic	-110 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers per IEC 62037
DTF, Connector A	-34 dB
DTF, Connector B	-34 dB

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
800–960 MHz	1.25	19.08
1700–2200 MHz	1.25	19.08
2500–2700 MHz	1.25	19.08

H4-NMNM-60-P

Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

