

L4-HMDM-8M-D

D-CLASS LDF4-50A SureFlex® Jumper with interface types 4.3-10 Male and 7-16 Din Male, 8 m



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	SureFlex® D-CLASS, dynamic PIM
Product Brand	HELIAX® SureFlex®
Product Series	LDF4-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	7-16 DIN Male
Specification Sheet Revision Level	B

Dimensions

Length	8 m 26.247 ft
Nominal Size	1/2 in

Electrical Specifications

3rd Order IMD Dynamic	-119 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers per IEC 62037
DTF, Connector A	-34 dB
DTF, Connector B	-34 dB

Logo Image

L4-HMDM-8M-D



VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.101	26.36
1700-2200 MHz	1.101	26.36
2200-2700 MHz	1.135	23.98
3400-3800 MHz	1.222	20.01

Jumper Assembly Sample Label

Batch Manufacturing Date (two digit year and week)
Manufacturing Plant Product Revision

0123456789 US22 1240 /A

COMMSCOPE Andrew Solutions™
F4-DMDM-2M-D Part Number
2 M (6.562 FT)
SUREFLEX ASSEMBLY
U.S. PATENT 5802710
Product of UNITED STATES
12US220001242 Serial Number



L4-HMDM-8M-D

Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant/Exempted



Included Products

LDF4-50A

- LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket Halogen free jacketing non-fire-retardant (General propose cable for outdoor use only)