

1-1933401-0



AMPINNERGY® Power-to-Line Cable Assembly, 8-wire/3-circuit (3-3-2), dedicated neutral, 10 feet

- Used to jumper system components together and can be used to extend power-to-power cable assemblies
- Mates with power connector and line connector cable assemblies, power junction boxes, power distribution modules, zone distribution modules, and power transition units

OBSOLETE

This product was discontinued on: June 30, 2020

Product Classification

Regional Availability	North America
Product Type	Power-to-line cable assembly
Product Brand	AMPINNERGY®
Product Series	AMPINNERGY

General Specifications

Application	Power to line connection
Construction Type	Corrugated hose
Interface, Connector A	Power male plug
Interface, Connector B	Line female plug
Neutral Type	Dedicated
Wiring	8-Wire/3 Circuit (3-3-2)

Dimensions

Cord Length	3.05 m 10.007 ft
Neutral Conductor Gauge, solid	10-12 AWG

Electrical Specifications

Current Rating, maximum	20 A
Voltage Rating, maximum	125 Vac 250 Vac

1-1933401-0

Environmental Specifications

Environmental Space Indoor

Safety Standard CEC 2015 | CSA 22.2 | NEC 2013 | UL 1286 | UL 183 | UL 498

Packaging and Weights

Packaging quantity 1

Packaging Type Bag