



ION®-M High Power Remote Unit for EDD 800 Band Applications

Product Classification

Product Type	Remote unit
Product Brand	ION®-M

General Specifications

Minimum Software Requirement	ION-M SW V6.50
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Type	High

Electrical Specifications

Impedance	50 ohm
License Band	EDD 800
Voltage Range	+100 to +240 Vac

Electrical Specifications, Rx (Uplink)

Operating Frequency Band	832 – 862 MHz (EDD 800)
Wavelength	1310 nm 1550 nm

Electrical Specifications, Tx (Downlink)

Operating Frequency Band	791 – 821 MHz (EDD 800)
---------------------------------	-------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted

