

7634508-02 | i-POI 19-U



i-POI™ CommScope Active Intelligent Point of Interface, PCS 1900 band, UMTS

OBSOLETE

Product Classification

Product Type	Active point of interface, intelligent
Product Brand	i-POI™

General Specifications

BTS Interface Location, Rx diversity	Front
BTS Interface Location, Rx/Tx combined	Rear
BTS Interface Location, Rx/Tx separated	Front Rear
DAS Interface Location, Rx diversity from DAS	Front
DAS Interface Location, Rx from DAS	Front
DAS Interface Location, Tx combined BTS signal	Front
DAS Interface, Tx combined BTS signal	QMA Female
DAS Interface, Tx combined BTS signal, quantity	2
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.

Electrical Specifications

Electrical Safety Standard	EN 60950
License Band	PCS 1900

Packaging and Weights

Height, packed	190 mm 7.48 in
-----------------------	------------------

7634508-02 | i-POI19-U

Width, packed	345 mm 13.583 in
Depth, packed	640 mm 25.197 in
Weight, gross	7.5 kg 16.535 lb
Weight, net	5.2 kg 11.464 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system