



ION-U® Series Digital Signal Measurement Receiver

OBSOLETE

Product Classification

Product Type	Receiver
Product Brand	ION-U®

General Specifications

Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
-------------	--

Electrical Specifications

Input Voltage	12 Vdc
Impedance	50 ohm
Operating Frequency Band	300 – 3800 MHz (Broadband)