

## ION® Active Intelligent Point of Interface Subrack and Guide Rail Kit, Four Post, for ION-U Applications

**OBSOLETE**

This product was discontinued on: June 30, 2022

### Product Classification

<b>Product Type</b>	Point of interface subrack
<b>Product Brand</b>	ION®

### General Specifications

<b>General Alarm</b>	Integrated into management system
<b>Interface Slots Available, quantity</b>	1
<b>Mounting</b>	Rack
<b>Note</b>	Detailed Product Specifications are available. Please contact your local CommScope representative.
<b>Rack Type</b>	EIA 19 in
<b>Slots Available, quantity</b>	8

### Dimensions

<b>Height</b>	177 mm   6.969 in
<b>Height, guide rails</b>	50 mm   1.969 in
<b>Width</b>	483 mm   19.016 in
<b>Width, guide rails</b>	335 mm   13.189 in
<b>Depth</b>	462 mm   18.189 in
<b>Depth, guide rails</b>	135 mm   5.315 in

### Electrical Specifications

<b>Electrical Safety Standard</b>	EN 60950
<b>Power Consumption</b>	276 W
<b>Voltage Range</b>	+10 to +14 Vdc

### Material Specifications

**Material Type** Stainless steel

## Environmental Specifications

**Operating Temperature** +5 °C to +50 °C (+41 °F to +122 °F)

**Storage Temperature** -25 °C to +70 °C (-13 °F to +158 °F)

**Relative Humidity** 46%–94%

**Mean Time Between Failures (MTBF) at Temperature** 213,000 h @ 25 °C

## Packaging and Weights

**Height, packed** 570 mm | 22.441 in

**Width, packed** 305 mm | 12.008 in

**Depth, packed** 620 mm | 24.409 in

**Included** Guide rails (4 post)

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system



## Included Products

7643288-01 – ION® Active Intelligent Point of Interface Subrack for ION-U  
SR 8/POI w/o guiderails Applications

# 7643288-01 | SR 8/POI w/o guiderails

## ION® Active Intelligent Point of Interface Subrack for ION-U Applications



### Product Classification

<b>Product Type</b>	Point of interface subrack
<b>Product Brand</b>	ION®

### General Specifications

<b>General Alarm</b>	Integrated into management system
<b>Interface Slots Available, quantity</b>	1
<b>Mounting</b>	Rack
<b>Note</b>	Detailed Product Specifications are available. Please contact your local CommScope representative.
<b>Rack Type</b>	EIA 19 in
<b>Slots Available, quantity</b>	8

### Dimensions

<b>Height</b>	177 mm   6.969 in
<b>Width</b>	483 mm   19.016 in
<b>Depth</b>	462 mm   18.189 in

### Electrical Specifications

<b>Electrical Safety Standard</b>	EN 60950
<b>Power Consumption</b>	276 W
<b>Voltage Range</b>	+10 to +14 Vdc

### Environmental Specifications

<b>Operating Temperature</b>	+5 °C to +50 °C (+41 °F to +122 °F)
------------------------------	-------------------------------------

# 7643288-01 | SR 8/POI w/o guiderails

---

<b>Storage Temperature</b>	-25 °C to +70 °C (-13 °F to +158 °F)
<b>Relative Humidity</b>	46%–94%
<b>Mean Time Between Failures (MTBF) at Temperature</b>	213,000 h @ 25 °C

## Packaging and Weights

<b>Height, packed</b>	570 mm   22.441 in
<b>Width, packed</b>	305 mm   12.008 in
<b>Depth, packed</b>	620 mm   24.409 in
<b>Weight, gross</b>	11.6 kg   25.574 lb
<b>Weight, net</b>	8 kg   17.637 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

