

# PFP-PX-8M

Power Express module, connects up to 8 Powered Fiber Cables



## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

### Product Type

Power supply module

## Dimensions

### Height

43.688 mm | 1.72 in

### Width

87.376 mm | 3.44 in

### Depth

322.326 mm | 12.69 in

### Compatible Gauge Range

24–8 AWG

## Electrical Specifications

### Input Current Range

0–20 A

### Input Voltage Range

-42 to -60 Vdc

### Output Voltage Range

-42 to 58 Vdc

### Output Voltage, nominal

-57 Vdc

### Electrical Safety Standard

CSA C22.2 No. 60950-1-03

### Electromagnetic Compatibility/Interference (EMC/EMI)

FCC-CFR, Part 15, sub-part B | GR1089 Class A

### Total Output Power

100 W, per circuit

## Environmental Specifications

### Operating Temperature

-40 °C to +75 °C (-40 °F to +167 °F)

### Relative Humidity

5%–95%, non-condensing

### Standards Compliance

EN 61000-4-2 level 4

# PFP-PX-8M

---

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Carton
<b>Weight, net</b>	1.134 kg   2.5 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

