

# PFP-SPS-1600M



## Slimline SPS DC Rectifier Module, 1600 Watts

### Product Classification

#### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

#### Product Type

Power supply module

### Dimensions

#### Height

41.656 mm | 1.64 in

#### Width

126.492 mm | 4.98 in

#### Depth

205.994 mm | 8.11 in

### Electrical Specifications

#### Input Current Range

15-12A @ 90-120Vac | 7.5A @ 230Vac

#### Output Voltage Range

-42 to 58 Vdc

#### Electrical Safety Standard

CE | CSA C22.2 No. 60950-1-03 | UL

#### Electromagnetic Compatibility/Interference (EMC/EMI)

FCC-CFR, Part 15, sub-part B | GR1089 Class A

#### Power Efficiency

95 %

### Environmental Specifications

#### Operating Temperature

-40 °C to +75 °C (-40 °F to +167 °F)

#### Standards Compliance

EN 61000-4-2 level 4 | GR 1089, Issue 4 | GR-63

### Packaging and Weights

#### Packaging quantity

1

#### Packaging Type

Carton

#### Weight, net

1.397 kg | 3.08 lb

# PFP-SPS-1600M

---

## Regulatory Compliance/Certifications

**Agency**

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

**Classification**

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant

