TFAH-US7B-14



ION®-B Series High Power Remote Unit for Cellular 700, LMR 800, Cellular 850, LMR 900, AWS, PCS 1900, and WiMAX

OBSOLETE


Product Classification	
Product Type	Remote unit
Product Brand	ION®-B
General Specifications	
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Class	High
Dimension Drawing	

Page 1 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 10, 2023



TFAH-US7B-14



Electrical Specifications

Impedance

Voltage Range

License Band

50 ohm

AWS | CEL 850 | Cellular 700 | LMR 800 | LMR 900 | PCS 1900 Extended | WiMAX

85 to 265 Vac

1710 - 1755 MHz (AWS 1700) | 1850 - 1915 MHz (PCS 1900 Extended) | 2496 - 2690 MHz (WiMAX) | 698 - 716 MHz (Cellular 700) | 776 - 787 MHz (Cellular 700) | 806 - 824 MHz (LMR 800) | 824 - 848.5 MHz (Cellular 850) | 896.5 - 902 MHz (LMR 900)

Electrical Specifications, Tx (Downlink)

Electrical Specifications, Rx (Uplink)

Operating Frequency Band

Operating Frequency Band

1930 – 1995 MHz (PCS 1900 Extended) 2110 – 2155 MHz (AWS
1700) 2496 – 2690 MHz (WiMAX) 728 – 757 MHz (Cellular
700) 851.5 - 869 MHz (LMR 800) 869 - 893.5 MHz (Cellular
850) 929 – 941 MHz (LMR 900)

Regulatory Compliance/Certifications

Page 2 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 10, 2023

COMMSCOPE[®]

TFAH-US7B-14

Agency

Classification

CHINA-ROHSAbove maximum concentration valueISO 9001:2015Designed, manufactured and/or distributed under this quality management systemROHSCompliant/ExemptedUK-ROHSCompliant/Exempted



Included Products

TPSN1/28-150

Power Supply Adapter ION®-B Series Remote Units, 150

W

_

Page 3 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 10, 2023

