CMAX-DMF-43-UW-I53



Low PIM Directional MIMO In-Building Antenna, 617–960 MHz, 1695–2700 MHz, 3300-4200MHz, and 4800-6000MHz 4.3-10, (2 PORTS 617-960 and 1695-2700MHz, 2 PORTS 3300-4200 and 4800-6000MHz)

Product Classification

Product Type In-building antenna

General Specifications

Antenna Array Characteristic

ApplicationIndoorAntenna TypeDirectional

Polarization ±45°

Color White (RAL 9016)

Number of Ports 4

Pigtail Cable670-141SXE, plenum ratedRadome MaterialASA+PC, UV stabilized

RF Connector Interface 4.3-10 Female

Dimensions

 Height
 120 mm | 4.724 in

 Width
 310 mm | 12.205 in

 Length
 450 mm | 17.717 in

 Pigtail Length
 450 mm | 17.717 in

Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 1695 – 2700 MHz | 3300 – 4000 MHz | 4800 – 6000 MHz | 617 – 698 MHz | 698 –

960 MHz

MIMO 2x2

Electrical Note Values typical, unless otherwise stated

Electrical Specifications

Frequency Band, MHz 617-698 698-960 1695-2200 2200-2700 3300-4200 4800-6000



CMAX-DMF-43-UW-I53

Gain, dBi	7.7	7.9	8.8	9	8	8.2
Beamwidth, Horizontal, degrees	75	73	62	64	64	62
Beamwidth, Vertical, degrees	72	66	57	64	65	61
Front-to-Back Ratio, Copolarization 180° ± 30°, dB	17	17	20	15	17	17
Isolation, Cross Polarization, dB	20	20	25	25	20	22
VSWR Return loss, dB	1.7 11.7	1.6 12.7	1.5 14.0	1.5 14.0	1.7 11.7	1.7 11.7
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	-153	-153
Input Power per Port, maximum, watts	100	100	100	100	100	100

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Relative Humidity Up to 100%

Packaging and Weights

 Height, packed
 190 mm | 7.48 in

 Width, packed
 340 mm | 13.386 in

 Length, packed
 645 mm | 25.394 in

 Included
 Mounting bracket

 Weight, gross
 4.6 kg | 10.141 lb

 Weight, net
 3.1 kg | 6.834 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



