

HC-08-S



Argus® Head Frame 800 / 900MHz

OBSOLETE

This product was discontinued on: May 31, 2016

Product Classification

Product Type Head frame

General Specifications

Application Outdoor

Dimensions

Height 2,398.01 mm | 94.41 in

Diameter, at zero degrees panning 552 mm | 21.732 in

Antenna Panning Capability ±15°

Weight, net 132 kg | 291.01 lb

Electrical Specifications

Lightning Protection Chassis ground

Mechanical Specifications

Wind Loading @ Velocity, maximum 1,100.0 N @ 160 km/h (247.3 lbf @ 160 km/h)

Wind Speed, maximum 288 km/h (179 mph)

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency **Classification**

HC-08-S

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system