



Carrier Access Point for High Power for EGSM-R Applications, Fiber Fed with Fan Kit

Product Classification

Regional Availability	EMEA
Product Type	Access point
Product Brand	ERA®
Product Series	CAP H

General Specifications

Fan Kit	Included
Fed Type	Fiber fed
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Class	High
Powering Type	Internal AC powered

Electrical Specifications

License Band	GSM-R
Voltage Range	100 to 240 Vac

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

