



PICABOND® Connector, 1000 strip, 48 Vdc, purple

- Lightweight, compact, and economical means of splicing multiconductor telephone cable
- No prestripping or cutting required, can tap without service interruptions, eliminates “turndowns”
- Color-coded to indicate size and type of wire; used for butt, straight, bridge and half-tap splicing applications

OBSOLETE

This product was discontinued on: June 1, 2016

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America North America
Product Type	Splice
Product Brand	PICABOND®
Product Series	PICABOND

General Specifications

Connector Color Code	Purple
Connector Sealant	Gel filled
Connector Splicing Type	Bridge Butt Full bridge Half-tap Straight (In-line)

Dimensions

Compatible Conductor Gauge, solid	26–22 AWG (AIR Core PIC) 26–24 AWG (Foam Filled PIC)
-----------------------------------	--

Electrical Specifications

Safety Voltage Rating	48 Vdc
-----------------------	--------

Material Specifications

Contact Base Material	Phosphor Bronze
Contact Plating Material	Tin
Insulation Material	Air Core PIC Foam Filled PIC

Environmental Specifications

Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Environmental Space	Outdoor

Packaging and Weights

Packaging quantity	1000
Packaging Type	Strip

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

