



PICABOND® Connector, 1000 loose piece, green, gel filled

- Lightweight, compact, and economical means of splicing multiconductor telephone cable
- No prestripping or cutting required, can tap without service interruptions, eliminates “turndowns”
- Color-coded to indicate size and type of wire; used for butt, straight, bridge and half-tap splicing applications

OBSOLETE

This product was discontinued on: June 1, 2016

Replaced By:

60945-4

PICABOND® Connector, 1000 loose piece, 400 Vdc, green

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America North America
Product Type	Splice
Product Brand	PICABOND®
Product Series	PICABOND

General Specifications

Connector Color Code	Green
Connector Sealant	Unfilled
Connector Splicing Type	Bridge Butt Full bridge Half-tap Straight (In-line)

Dimensions

Compatible Conductor Gauge, solid	26–22 AWG
--	-----------

Electrical Specifications

Safety Voltage Rating	48 Vdc
------------------------------	--------

Material Specifications

Contact Base Material	Brass
Contact Plating Material	Tin

60945-1

Insulation Material

Air Core PIC | Paper or Pulp

Environmental Specifications

Operating Temperature

-40 °C to +60 °C (-40 °F to +140 °F)

Environmental Space

Outdoor

Packaging and Weights

Packaging quantity

1000

Packaging Type

Loose piece

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

