

# 108009424 | M81 BNC-B COUPLER

---



M81 BNC-B Coupler 50 Ohm

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Multimedia coupler

## General Specifications

<b>Application</b>	Module designed for data applications
<b>Mounting</b>	Snap-in

## Dimensions

<b>Height</b>	17.526 mm   0.69 in
<b>Width</b>	18.542 mm   0.73 in
<b>Depth</b>	15.24 mm   0.6 in

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	5%–95%, non-condensing

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system