

## HGS620 M-Series Adapter, Violet (25 ea/pkg)



### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Adapter
<b>Ordering Note</b>	Minimum order quantity, 20 packs

### General Specifications

<b>Color</b>	Violet
<b>Integrated Dust Cover Type</b>	None

### Dimensions

<b>Height</b>	17.53 mm   0.69 in
<b>Width</b>	18.54 mm   0.73 in
<b>Depth</b>	9.14 mm   0.36 in

### Material Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic
----------------------	---

### Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	UL   cUL

### Packaging and Weights

**Packaging quantity** 25

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

