760245962 | G2-SP-12SAG-PT



G2 Splice Cassette, 12SC/APC, OS2, with pigtails

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber cassette with pigtails

Product Series G2

General Specifications

Color, frontGreenInterface, frontSC/APC

Interface, rearStranded pigtailPolarityPairs, straight

Shuttered No Total Fibers, quantity 12

Dimensions

 Height
 26.416 mm | 1.04 in

 Width
 96.52 mm | 3.8 in

 Depth
 165.354 mm | 6.51 in

Material Specifications

Alignment Sleeve Material Zirconia

Optical Specifications

Fiber ModeSinglemodeFiber TypeG.657.A2Insertion Loss, maximum0.3 dBReturn Loss, minimum60 dB



760245962 | G2-SP-12SAG-PT

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard UL

Packaging and Weights

Included SMOUV holder | SMOUV splice protection

Packaging quantity 1

Weight, net 0.116 kg | 0.256 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

