860643027 | OC-ADP-L2-L2-NFCD-(6)



Fiber Optic Duplex Adapter, Singlemode LC/APC, green, flangeless, 6 pcs

- High quality zirconia ceramic split sleeves ensuring high precision alignment, reliability and improved reconnect ability
- Translucent easy grip dust cap and integrated mounting clips
- High quality one piece housing, no ultrasonic welding

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Fiber adapter

Product Series OC-ADP

General Specifications

Body StyleDuplexColorGreenInterfaceLC/APC

Mounting Square flange


Total Ports, quantity 2


Transmission Standards IEC 60754-1 | IEC 61300-3-42

Outline Drawing



860643027 | OC-ADP-L2-L2-NFCD-(6)





Material Specifications

Alignment Sleeve Material Ceramic

Mechanical Specifications

Coupling Retention Force 70 N | 15.737 lbf

Optical Specifications

Fiber Mode Singlemode

Insertion Loss, maximum 0.1 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Packaging and Weights

Packaging quantity 6

Packaging Type Bag

