

# CC3540-000 | OC-ADK-S5-S5-NNCS-(24)

---

Fiber Optic Simplex Adapter, Multimode SC/UPC, aqua, with FIST retainer (24 pcs)

- High quality zirconia ceramic split sleeves ensuring high precision alignment, reliability and improved reconnect ability
- Translucent easy grip dust cap and integrated mounting clips
- High quality one piece housing, no ultrasonic welding

## Product Classification

**Regional Availability** Asia | Australia/New Zealand | EMEA | Latin America | North America

**Product Type** Fiber adapter

**Product Series** OC-ADK

## General Specifications

**Body Style** Simplex

**Color** Aqua

**Interface** SC/UPC

**Mounting** Square flange

**Total Ports, quantity** 1

**Transmission Standards** IEC 60754-1 | IEC 61300-3-42

## Material Specifications

**Alignment Sleeve Material** Ceramic

## Mechanical Specifications

**Coupling Retention Force** 70 N | 15.737 lbf

## Optical Specifications

**Fiber Mode** Multimode

**Insertion Loss, maximum** 0.1 dB

## Environmental Specifications

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

## Packaging and Weights

**Packaging quantity** 24

**Packaging Type**                      Bag

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

