

E46733-000 | OC-ADK-E9-E9-NNCS

Fiber Optic Simplex Adapter, Singlemode LSH/APC, green, with FIST retainer

- High quality zirconia ceramic split sleeves ensuring high precision alignment, reliability and improved reconnect ability

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Fiber adapter
Product Series	OC-ADK

General Specifications

Body Style	Simplex
Color	Green
Interface	LSH/APC
Mounting	Square flange
Total Ports, quantity	1
Transmission Standards	IEC 60754-1 IEC 61300-3-42

Material Specifications

Alignment Sleeve Material	Ceramic
----------------------------------	---------

Mechanical Specifications

Coupling Retention Force	70 N 15.737 lbf
---------------------------------	-------------------

Optical Specifications

Fiber Mode	Singlemode
Insertion Loss, maximum	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
------------------------------	--------------------------------------

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag

Regulatory Compliance/Certifications

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

