023826-000 | OC-ADP-S2-S2-NNCS



Fiber Optic Simplex Adapter, Singlemode SC/APC, green, with flanges

- High quality zirconia ceramic split sleeves ensuring high precision alignment, reliability and improved reconnect ability
- Translucent easy grip dust cap and integrated mounting clips
- High quality one piece housing, no ultrasonic welding

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Fiber adapter
Product Series OC-ADP

General Specifications

Body StyleSimplexColorGreenInterfaceSC/APC

Mounting Square flange

Total Ports, quantity 1

Transmission Standards IEC 60754-1 | IEC 61300-3-42

Material Specifications

Alignment Sleeve Material Ceramic

Mechanical Specifications

Coupling Retention Force 70 N | 15.737 lbf

Optical Specifications

Fiber Mode Singlemode

Insertion Loss, maximum 0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Packaging and Weights



023826-000 | OC-ADP-S2-S2-NNCS

Packaging quantity

Packaging Type Bag

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

1

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

