


760248322 | G2-SP-12SCW-PT-ANT



G2 Splice Cassette, 12SC/UPC, OS2, with pigtails

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber cassette with pigtails
Product Series	G2

General Specifications

Color, front	Blue
Interface, front	SC/UPC
Interface, rear	Stranded pigtail
Polarity	Pairs, straight
Shuttered	No
Total Fibers, quantity	12

Dimensions

Height	26.416 mm 1.04 in
Width	96.52 mm 3.8 in
Depth	165.354 mm 6.51 in

Material Specifications

Alignment Sleeve Material	Zirconia
----------------------------------	----------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G657 A1 easy strip buffer fiber OS2
Insertion Loss, maximum	0.55 dB

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard UL

Packaging and Weights

Included ANT holder

Packaging quantity 1

Weight, net 0.116 kg | 0.256 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

