FD3-AJ864J00PFBP5X



FDH 3000 Large PFP cabinet, 864-Pos, SC/APC, No Splitters, Dry-Dry Single Armor Ribbon OSP, 100ft, 288f. Feeder, (2) 432f. Distribution, 48.74"H* x 47.39"W x 19.58"D *Includes 6" tall riser

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series FDH 3000

General Specifications

Access Front and rear door

Cable Type Armored - Ribbon

Distribution Cables, quantity2Distribution Ports, quantity864Fibers per Distribution Cable, quantity432Fibers per Feeder Cable, quantity288

Interface, Input SC
Interface Feature, Input APC

Mounting Pad

Dimensions

Cable Length

 Height
 1,238.25 mm | 48.75 in

 Width
 1,220.47 mm | 48.05 in

 Depth
 497.33 mm | 19.58 in

137.00 11111 | 13.00 11

Enclosure Size Large

Material Specifications

Finish Powder coated

Material Type Aluminum



30.48 m | 100 ft

FD3-AJ864J00PFBP5X

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

