



FIELD TERM RJ45 Modular Plug CAT6A BAG OF 100+TOOL

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Modular plug

General Specifications

ANSI/TIA Category	6A
Cable Type	U/UTP (unshielded)
Conductor Type	Solid Stranded
Interface	RJ45
Positions/Loaded Contacts	8
Termination Type	IDC

Dimensions

Compatible Cable Diameter, maximum	7.4 mm 0.291 in
Compatible Cable Diameter, minimum	7.1 mm 0.28 in
Compatible Insulated Conductor Diameter, maximum	0.89 mm 0.035 in
Compatible Insulated Conductor Diameter, minimum	0.84 mm 0.033 in
Contact Plating Thickness	1.27 µm
Compatible Conductor Gauge, solid	23 AWG

Material Specifications

Contact Base Material	Copper alloy
Contact Plating Material	Gold over nickel
Material Type	Polycarbonate

760244131

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Environmental Specifications

Safety Standard UL 114344

Packaging and Weights

Packaging quantity 100

Packaging Type Bag