

760248225 | TERM-TOOL-KIT-PR QWIK II™



Premium Termination Toolkit for Field Installable Qwik II Connectors

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber tool kit
Product Brand	Qwik II
Product Series	Qwik II

General Specifications

Compatible Interface	Qwik II LC Qwik II SC Qwik II ST
----------------------	--------------------------------------


Packaging and Weights

Included	0.25/0.9 mm cable clamp 2/3mm cable clamp Fiber cleaning fluid Fiber stripper Instruction sheet Lint-free cotton wipes Marker Precision Fiber cleaver Premium hard case Scissors Strip length template Visual fault indicator and adapter
----------	---

Included Products

760243349 QWIK II™ 900 um Fiber Clamp	–	Fiber clamp, buffer tube, 900 um
760243350 QWIK II™ 2.0 mm Fiber Clamp	–	Fiber clamp, 2.0 mm
760243351 QWIK II™ 3.0 mm Fiber Clamp	–	Fiber clamp, 3.0 mm
760249056	–	Fiber Optic Visual Fault Locator with 2.5 and 1.25 mm Adapter Caps, for connectors such as SC, ST, FC, LC and MU
760249518 FC-8R	–	Fiber Optic Automatic Blade Rotation Cleaver

760243349 | QWIK II™ 900 um Fiber Clamp



Fiber clamp, buffer tube, 900 um

Product Classification


Regional Availability	North America
Product Type	Fiber tool kit
Product Brand	Qwik
Product Series	Qwik II

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



760243350 | QWIK II™ 2.0 mm Fiber Clamp



Fiber clamp, 2.0 mm

Product Classification


Regional Availability	North America
Product Type	Fiber tool kit
Product Brand	Qwik
Product Series	Qwik II

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



760243351 | QWIK II™ 3.0 mm Fiber Clamp



Fiber clamp, 3.0 mm

Product Classification

Regional Availability	North America
Product Type	Fiber tool kit
Product Brand	Qwik
Product Series	Qwik II

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant





Fiber Optic Visual Fault Locator with 2.5 and 1.25 mm Adapter Caps, for connectors such as SC, ST, FC, LC and MU

- Locate sharp bends, breaks, and damages in fiber
- Conduct end-to-end continuity tests
- Perform fiber tracing and identification
- Compact, ergonomic design for ultimate portability
- Visible wavelength is 650 nm
- High powered laser (1 mW) for single-mode (> 7 km) and multi-mode (> 5 km) connectors
- Continuous or Flash illumination
- 2.5 mm and 1.25 mm connector inputs

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA North America
Portfolio	CommScope®
Product Type	Tool kit

General Specifications

Compatible Connector Type	FC LC SC ST
---------------------------	-------------------

Environmental Specifications

Environmental Space	Indoor
---------------------	--------

Packaging and Weights

Included	2 AAA Batteries Pouch VFL with 1.25 mm and 2.5 mm Adapter Caps
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant





Fiber Optic Automatic Blade Rotation Cleaver

- Smart Cleave Counter
- 1 to 12-Fiber Ribbon Cleaver
- Automatic Blade Rotation
- Compatible with All Sumitomo Electric Fusion Splicers
- Precision Blade Performs 60,000 Cleaves
- 125 μm cladding diameter
- 90° ± 0.5° cleave angle (Typ.)
- Single fiber adapter (AP-FC7) for 250μm to 900μm coating diameters

Product Classification

Regional Availability	Asia EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber tool kit

Dimensions

Height	47 mm 1.85 in
Width	58 mm 2.283 in
Length	98 mm 3.858 in

Environmental Specifications

Environmental Space	Indoor
---------------------	--------

Packaging and Weights

Packaging quantity	1
Weight, net	260 g 0.573 lb