



HELIAX® Outdoor Excess Cable Enclosure, 14 in x 6 in x 3 in

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Outdoor junction box
Product Brand	HELIAX®

General Specifications

Application	Accepts 20 m of excess fiber tails
Cable Entry, quantity, maximum, left	1
Cable Entry, quantity, maximum, right	1
Mounting	Pipe, 44–88.9 mm (1.75–3.5 in) OD

Dimensions

Height	149.86 mm 5.9 in
Width	355.6 mm 14 in
Depth	81.28 mm 3.2 in

Material Specifications

Material Type	Aluminum
----------------------	----------

Environmental Specifications

Environmental Space	Indoor Outdoor
Qualification Standards	IEC 60529:2001, IP64

Packaging and Weights

Included	Mounting kit
Weight, net	3.121 kg 6.88 lb

FE-1463-01

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system