

FGS-HTHR-5/8-48



FiberGuide® Threaded Rod, 5/8in Diameter, 48in Length

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Threaded rod
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Color	Silver
Orientation	Horizontal
Section Type	Mounting

Dimensions

Length	mm 48 in
Rod Length	1,219.2 mm 48 in
Thread Size	5/8 in
System Dimensions	102 mm x 102 mm (4 in x 4 in) 102 mm x 152 mm (4 in x 6 in) 51 mm x 152 mm (2 in x 6 in)

Ordering Tree

FGS-HTHR-5/8-48

FGS - HTHR - $\overset{9}{\boxed{5/8}}$ - $\overset{10}{\boxed{72}}$

Rod Diameter

9	1/2	1/2 in
	5/8	5/8 in
	12 MM	12 mm
	14 MM	14 mm
	16 MM	16 mm

Rod Length

10	12	12 in
	30	30 in
	48	48 in
	72	72 in
	30CM	30 cm
	75CM	75 cm
	180CM	180 cm

* Rod diameter and length needs to be both metric or imperial sized

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

