

CHD ULL Multimode, MPO-8 distribution module, 8LC to 1x8f MPO unpinned with port blockers, dust plugs

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber module
<b>Product Brand</b>	SYSTIMAX ULL
<b>Product Series</b>	CHD

## General Specifications

<b>Adapters, quantity, front</b>	8
<b>Color, front</b>	Aqua
<b>Color, rear</b>	Gray
<b>Interface, front</b>	LC
<b>Interface Feature, front</b>	Standard
<b>Interface, rear</b>	MPO Unpinned
<b>Interface Feature, rear</b>	Key up/up
<b>Polarity</b>	Method B Enhanced
<b>Shuttered</b>	No
<b>Total Fibers, quantity</b>	8

## Dimensions

<b>Height</b>	12.45 mm   0.49 in
<b>Width</b>	83.82 mm   3.3 in
<b>Depth</b>	131.83 mm   5.19 in

## Optical Specifications

<b>Fiber Type</b>	OM4
<b>Insertion Loss, maximum</b>	0.35 dB

## Environmental Specifications

<b>Qualification Standards</b>	IEC 61753-1   TIA-568.3-D
--------------------------------	---------------------------

# 760248405 | CHD08-DM-PBLC-LS-B-ULL

---

**Safety Standard** CE | CSA | UL

Packaging and Weights

**Packaging quantity** 1