

CHD ULL Multimode, MPO-8 distribution module, 8LC to 1x8f MPO unpinned with port blockers, dust plugs

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	SYSTIMAX ULL
Product Series	CHD

General Specifications

Adapters, quantity, front	8
Color, front	Lime green
Color, rear	Gray
Interface, front	LC
Interface Feature, front	Standard
Interface, rear	MPO Unpinned
Interface Feature, rear	Key up/up
Polarity	Method B Enhanced
Shuttered	No
Total Fibers, quantity	8

Dimensions

Height	12.45 mm 0.49 in
Width	83.82 mm 3.3 in
Depth	131.83 mm 5.19 in

Optical Specifications

Fiber Type	OM4
Insertion Loss, maximum	0.35 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
--------------------------------	---------------------------

760248406 | CHD08-DM-PBLC-WB-B-ULL

Safety Standard CE | CSA | UL

Packaging and Weights

Packaging quantity 1