


ETL Verified Category 5e U/UTP Cable, non-plenum, yellow jacket, 4 pair count, 1000 ft (305 m) length, CommPak



Product Classification

Product Type Twisted pair cable


General Specifications

ANSI/TIA Category 5e
Cable Type U/UTP (unshielded)
Jacket Color Yellow
Pairs, quantity 4
Transmission Standards ANSI/TIA-568.2-D

Dimensions

Cable Length 304.8 m | 1000 ft

Cross Section Drawing



Electrical Cable Performance

- CS** CommScope
- STD** Refers to the standard value listed under Transmission Standards in the Electrical Specifications above
- TYP** Typical Electrical Performance
- IL** Insertion Loss (dB/100m)
- ACR** Attenuation to Crosstalk Ratio (dB/100m)
- PSACR** Power Sum Attenuation to Crosstalk Ratio (dB/100m)
- PSACRF** Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)
- TCL** Transverse Conversion Loss (dB/100m)
- NEXT** Near End Crosstalk (dB/100m)
- PSNEXT** Power Sum Near End Crosstalk (db/100m)
- ACRF** Attenuation to Crosstalk Ratio - Far End (dB/100m)
- RL** Return Loss (dB)
- ELTCTL** Equal Level Transverse Conversion Transfer Loss (dB/100m)

Freq. MHz	IL			NEXT			ACR			PSNEXT			PSACR			ACRF			PSACRF			RL		
	CS	STD	TYP	CS	STD	TYP	CS	STD	TYP	CS	STD	TYP	CS	STD	TYP	CS	STD	TYP	CS	STD	TYP	CS	STD	TYP
1	2	2	1.8	70.3	65.3	85	68.3	63.3	83.1	68.3	62.3	82.6	66.3	60.3	80.8	67.8	63.8	79.8	65.8	60.8	78	20	20	34.8
4	3.9	4.1	3.7	61.3	56.3	75.9	57.3	52.2	72.2	59.3	53.3	73.4	55.3	49.2	69.7	55.8	51.8	68.1	53.8	48.8	66.3	23.3	23	35.1
8	5.6	5.8	5.3	56.8	51.8	70.8	51.2	46	65.6	54.8	48.8	68.5	49.2	43	63.3	49.7	45.7	62.2	47.7	42.7	60.5	25	24.5	35.9
10	6.2	6.5	5.9	55.3	50.3	69.7	49.1	43.8	63.8	53.3	47.3	67.4	47.1	40.8	61.5	47.8	43.8	60.3	45.8	40.8	58.5	25.5	25	36.8
16	7.9	8.2	7.6	52.2	47.2	66.3	44.3	39	58.7	50.2	44.2	64	42.3	36	56.4	43.7	39.7	56.3	41.7	36.7	54.5	25.5	25	37.9
20	8.9	9.3	8.5	50.8	45.8	64.8	41.9	36.5	56.3	48.8	42.8	62.4	39.9	33.5	53.9	41.8	37.8	54.4	39.8	34.8	52.5	25.5	25	37.6
25	10	10.4	9.5	49.3	44.3	63.3	39.3	33.9	53.8	47.3	41.3	61	37.3	30.9	51.5	39.8	35.8	52.5	37.8	32.8	50.6	24.8	24.3	37.9
31.25	11.3	11.7	10.7	47.9	42.9	61.8	36.6	31.2	51.2	45.9	39.9	59.5	34.6	28.2	48.9	37.9	33.9	50.5	35.9	30.9	48.6	24.1	23.6	37.7
62.5	16.3	17	15.3	43.4	38.4	57.3	27.1	21.4	42	41.4	35.4	55.1	25.1	18.4	39.7	31.9	27.9	44.4	29.9	24.9	42.5	22	21.5	33.5
100	21	22	19.6	40.3	35.3	54.5	19.3	13.3	34.9	38.3	32.3	52.1	17.3	10.3	32.5	27.8	23.8	40.4	25.8	20.8	38.4	20.6	20.1	31
155	26.8		24.8	37.4		51.2	10.7		26.4	35.4		49	8.7		24.1	24		36.7	22		34.7	19.3		28.9
200	30.9		28.4	35.8		48.9	4.9		20.4	33.8		46.6	2.9		18.2	21.8		34.2	19.8		32.2	18.5		28.6
250	35		32	34.3		47.4	-0.7		15.4	32.3		45.1	-2.7		13.1	19.8		32	17.8		30	17.8		28
300	38.9		35.3	33.1		45.8	-5.8		10.5	31.1		43.5	-7.8		8.2	18.3		30.1	16.3		28.2	17.3		28.1
350	42.6		38.4	32.1		44.1	-10.4		5.7	30.1		41.9	-12.4		3.5	16.9		28.4	14.9		26.5	16.8		27.4

Environmental Specifications

Environmental Space Non-plenum

Packaging and Weights

Packaging Type CommPak® box

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system