FPX-1FSJ/02AU016



FPX Fiber Optic Termination Panel with IFC Stranded Cable, 1RU, 19in, Singlemode, 24 fiber, SC/APC connectors, Stub tail at far end, putty white, 16m

Product Classification

Depth

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel, with IFC cable
Product Series	FPX
General Specifications	
Functionality	Patching
Adapter Packs Included, quantity	2
Body Style	Symmetrical
Cable Exit Location	Upward
Cable Stub Type	IFC
Color	Putty white
Color, front	Putty white
Growth Configuration	Fully loaded
Interface, front	SC/APC
Interface, rear	Stub tail
Patching Capacity, maximum	24
Rack Type	EIA 19 in EIA 23 in
Rack Units	1
Shelf Movement	Sliding
Total Fibers, quantity	24
Total Ports, quantity	24
Dimensions	
Height	44.45 mm 1.75 in
Width	482.6 mm 19 in

Page 1 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 12, 2023

304.8 mm | 12 in


COMMSCOPE°

FPX-1FSJ/02AU016

Cable Length

16 m | 52.493 ft

Ordering Tree



Material Specifications

Finish	Powder coated
Material Type	Steel
Optical Specifications	
Fiber Mode	Singlemode

Environmental Specifications

Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 12, 2023



FPX-1FSJ/02AU016

Storage Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

1

Page 3 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 12, 2023

