

FPX-3FS8/0AMU214



FPX Fiber Optic Termination Panel with IFC Ribbon Cable, 3RU, 19in, Singlemode, 144 fiber, LC/UPC connectors, Stub tail at far end, putty white, 214m

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel, with IFC cable
Product Series	FPX

General Specifications


Functionality	Patching
Adapter Packs Included, quantity	6
Body Style	Symmetrical
Cable Exit Location	Upward
Cable Stub Type	IFC
Color	Putty white
Growth Configuration	Fully loaded
Interface, front	LC/UPC
Interface, rear	Stub tail
Rack Type	EIA 19 in EIA 23 in
Rack Units	3
Shelf Movement	Sliding
Total Fibers, quantity	144
Total Ports, quantity	144

Dimensions

Height	133.35 mm 5.25 in
Width	482.6 mm 19 in
Depth	304.8 mm 12 in
Cable Length	214 m 702.1 ft

FPX-3FS8/0AMU214

Ordering Tree



Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

Fiber Mode	Singlemode
------------	------------

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

FPX-3FS8/0AMU214

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

