FPX-5FS7/0AAU031



FPX Fiber Optic Termination Panel with IFC Stranded Cable, 5RU, 19in, Singlemode, 144 fiber, SC/UPC connectors, Stub tail at far end, putty white, 31m

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with IFC cable

Product Series FPX

General Specifications

Functionality Patching

Adapter Packs Included, quantity 12

Body Style Symmetrical

Cable Exit Location Upward

Cable Stub Type IFC

Color Putty white

Color, front Putty white

Interface, front SC/UPC

Interface, rear Stub tail

Patching Capacity, maximum 144

Rack Type EIA 19 in | EIA 23 in

Rack Units 5

Shelf Movement Sliding

Total Fibers, quantity 144

Total Ports, quantity 144

Dimensions

Growth Configuration

 Height
 222.25 mm | 8.75 in

 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in

Page 1 of 3


Fully loaded

FPX-5FS7/0AAU031

Cable Length

31 m | 101.706 ft

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications



FPX-5FS7/0AAU031

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

