FPX-5FS7/0ARU092



FPX Fiber Optic Termination Panel with Indoor/Outdoor Cable, 5RU, 19in, Singlemode, 144 fiber, SC/UPC connectors, Stub tail at far end, putty white, 92m

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with indoor/outdoor cable

Product Series FPX

General Specifications

Functionality Patching

Adapter Packs Included, quantity 12

Body Style Symmetrical

Cable Exit Location Upward

Cable Stub Type Indoor/Outdoor

ColorPutty whiteColor, frontPutty whiteGrowth ConfigurationFully loaded

Interface, frontSC/UPCInterface, rearStub tail

Patching Capacity, maximum 144

Rack Type EIA 19 in | EIA 23 in

Rack Units 5

Shelf MovementSlidingTotal Fibers, quantity144Total Ports, quantity144

Dimensions

 Height
 222.25 mm | 8.75 in

 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in

Page 1 of 3




FPX-5FS7/0ARU092

Cable Length

92 m | 301.837 ft

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications



FPX-5FS7/0ARU092

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

