## FPX-5FS8/0HHU031



FPX Fiber Optic Termination Panel with Indoor/Outdoor Cable, 5RU, 19in, Singlemode, 288 fiber, LC/UPC connectors, Stub tail at far end, putty white, 31m

#### Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber patch panel, with indoor/outdoor cable

**Product Series** FPX

## General Specifications

**Functionality** Patching

Adapter Packs Included, quantity 12

**Body Style** Symmetrical

Cable Exit Location Upward

Cable Stub Type Indoor/Outdoor

ColorPutty whiteColor, frontPutty whiteGrowth ConfigurationFully loaded

Interface, frontLC/UPCInterface, rearStub tail

Patching Capacity, maximum 288

Rack Type EIA 19 in | EIA 23 in

Rack Units 5

Shelf MovementSlidingTotal Fibers, quantity288Total Ports, quantity288

#### **Dimensions**

 Height
 222.25 mm | 8.75 in

 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in

Page 1 of 3




# FPX-5FS8/0HHU031

#### **Cable Length**

31 m | 101.706 ft

## Ordering Tree



### Material Specifications

**Finish** Powder coated

Material Type Steel

Optical Specifications

**Fiber Mode** Singlemode

**Environmental Specifications** 



# FPX-5FS8/0HHU031

Operating Temperature  $-40 \, ^{\circ}\text{C} \text{ to } +85 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F to } +185 \, ^{\circ}\text{F})$ 

**Storage Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$ 

Packaging and Weights

Packaging quantity 1

