FPX-5FSJ/0AJU122



FPX Fiber Optic Termination Panel with OSP Stranded Cable, 5RU, 19in, Singlemode, 144 fiber, SC/APC connectors, Stub tail at far end, putty white, 122m

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with IFC cable

Product Series FPX

General Specifications

Functionality Patching

Adapter Packs Included, quantity 12

Body Style Symmetrical

Cable Exit Location Upward

Cable Stub Type IFC

ColorPutty whiteColor, frontPutty white

Growth Configuration Fully loaded

Interface, front SC/APC

Interface, rear Stub tail

Patching Capacity, maximum 144

Rack Type EIA 19 in | EIA 23 in

Rack Units 5

Shelf Movement Sliding

Total Fibers, quantity 144

Total Ports, quantity 144

Dimensions

 Height
 222.25 mm | 8.75 in

 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in

Page 1 of 3




FPX-5FSJ/0AJU122

Cable Length

122 m | 400.262 ft

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications



FPX-5FSJ/0AJU122

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

