FPX-9FS7/0CRU016



FPX Fiber Optic Termination Panel with Indoor/Outdoor Cable, 9RU, 19in, Singlemode, 216 fiber, SC/UPC connectors, Stub tail at far end, putty white, 16m

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel, with indoor/outdoor cable
Product Series	FPX
General Specifications	
Functionality	Patching
Adapter Packs Included, quantity	18
Body Style	Symmetrical
Cable Exit Location	Upward
Cable Stub Type	Indoor/Outdoor
Color	Putty white
Growth Configuration	Fully loaded
Interface, front	SC/UPC
Interface, rear	Stub tail
Rack Type	EIA 19 in EIA 23 in
Rack Units	9
Shelf Movement	Sliding
Total Fibers, quantity	216
Total Ports, quantity	216
Dimensions	
Height	400.05 mm 15.75 in
Width	482.6 mm 19 in
Depth	304.8 mm 12 in
Cable Length	16 m 52.493 ft


Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 5, 2024



FPX-9FS7/0CRU016

Ordering Tree



Material Specifications

Finish

Powder coated

Material Type

material Type

Steel

Optical Specifications

Fiber Mode

Singlemode

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 5, 2024



FPX-9FS7/0CRU016

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Classification

Agency

CHINA-ROHS REACH-SVHC Below maximum concentration value Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

UK-ROHS

Compliant Compliant



Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 5, 2024

