## FPX-9FS7/0CRU031



FPX Fiber Optic Termination Panel with Indoor/Outdoor Cable, 9RU, 19in, Singlemode, 216 fiber, SC/UPC connectors, Stub tail at far end, putty white, 31m

### Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber patch panel, with indoor/outdoor cable

**Product Series** FPX

General Specifications

**Functionality** Patching

Adapter Packs Included, quantity 18

**Body Style** Symmetrical

Cable Exit Location Upward

Cable Stub Type Indoor/Outdoor

**Color** Putty white

**Color, front** Putty white

**Growth Configuration** Fully loaded

Interface, front SC/UPC

Interface, rear Stub tail

Patching Capacity, maximum 216

Rack Type EIA 19 in | EIA 23 in

Rack Units 9

Shelf MovementSlidingTotal Fibers, quantity216Total Ports, quantity216

Dimensions

 Height
 400.05 mm | 15.75 in

 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in




## FPX-9FS7/0CRU031

#### Cable Length

31 m | 101.706 ft

### Ordering Tree



## Material Specifications

**Finish** Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

**Environmental Specifications** 

**Operating Temperature**  $-40 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

**COMMSCOPE®** 

# FPX-9FS7/0CRU031

**Storage Temperature** 

-40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted

UK-ROHS Compliant

