FPX-9FS7/0CRU092



FPX Fiber Optic Termination Panel with Indoor/Outdoor Cable, 9RU, 19in, Singlemode, 216 fiber, SC/UPC connectors, Stub tail at far end, putty white, 92m

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with indoor/outdoor cable

Product Series FPX

General Specifications

Functionality Patching

Adapter Packs Included, quantity 18

Body Style Symmetrical

Cable Exit Location Upward

Cable Stub Type Indoor/Outdoor

Color Putty white

Growth Configuration Fully loaded

Interface, front SC/UPC

Interface, rear Stub tail

Rack Type EIA 19 in | EIA 23 in

Rack Units 9

Shelf Movement Sliding

Total Fibers, quantity 216

Total Ports, quantity 216

Dimensions

Height 400.05 mm | 15.75 in

Width 482.6 mm | 19 in


Depth 304.8 mm | 12 in

Cable Length 92 m | 301.837 ft



FPX-9FS7/0CRU092

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Page 2 of 3



FPX-9FS7/0CRU092

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

