### FPXB-1FSJ/01HU092



FPX Fiber Optic Termination Panel with Indoor/Outdoor Cable, 1RU, 19in, Singlemode, 12 fiber, SC/APC connectors, Stub tail at far end, black, 92m

#### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber patch panel, with indoor/outdoor cable

**Product Series** FPX

General Specifications

**Functionality** Patching

Adapter Packs Included, quantity 2

**Body Style** Symmetrical

Cable Exit Location Upward

Cable Stub Type Indoor/Outdoor

**Color** Black

**Growth Configuration** Partially loaded

Interface, frontSC/APCInterface, rearStub tail

Rack Type EIA 19 in | EIA 23 in

Rack Units 1

Shelf Movement Sliding

Total Fibers, quantity 12

Total Ports, quantity 12

**Dimensions** 

 Height
 44.45 mm | 1.75 in

 Width
 482.6 mm | 19 in


 Depth
 304.8 mm | 12 in

 Cable Length
 92 m | 301.837 ft



## FPXB-1FSJ/01HU092

### Ordering Tree



### Material Specifications

**Finish** Powder coated

Material Type Steel

**Optical Specifications** 

**Fiber Mode** Singlemode

#### **Environmental Specifications**

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

Page 2 of 3

# FPXB-1FSJ/01HU092

### Packaging and Weights

Packaging quantity

#### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

