FPXB-2FS7/04HU092



FPX Fiber Optic Termination Panel with Indoor/Outdoor Cable, 2RU, 19in, Singlemode, 48 fiber, SC/UPC connectors, Stub tail at far end, black, 92m

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with indoor/outdoor cable

Product Series FPX

General Specifications

Functionality Patching

Adapter Packs Included, quantity

Body Style Symmetrical

Cable Exit Location Upward

Cable Stub TypeIndoor/Outdoor

Color Black

Growth Configuration Fully loaded

Interface, frontSC/UPCInterface, rearStub tail

Rack Units 2

Shelf Movement Sliding

Total Fibers, quantity 48

Total Ports, quantity 48

Dimensions

Rack Type

 Height
 88.9 mm | 3.5 in

 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in


 Cable Length
 92 m | 301.837 ft

COMMSCOPE®

EIA 19 in | EIA 23 in

FPXB-2FS7/04HU092

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Page 2 of 3

FPXB-2FS7/04HU092

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

