FPXB-4FS7/09HU153



FPX Fiber Optic Termination Panel with Indoor/Outdoor Cable, 4RU, 19in, Singlemode, 96 fiber, SC/UPC connectors, Stub tail at far end, black, 153m

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel, with indoor/outdoor cable
Product Series	FPX
General Specifications	
Functionality	Patching
Adapter Packs Included, quantity	8
Body Style	Symmetrical
Cable Exit Location	Upward
Cable Stub Type	Indoor/Outdoor
Color	Black
Color, front	Black
Growth Configuration	Fully loaded
Interface, front	SC/UPC
Interface, rear	Stub tail
Patching Capacity, maximum	96
Rack Type	EIA 19 in EIA 23 in
Rack Units	4
Shelf Movement	Sliding
Total Fibers, quantity	96
Total Ports, quantity	96
Dimensions	
Height	177.8 mm 7 in
Width	482.6 mm 19 in

Page 1 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 12, 2023

COMMSCOPE®

FPXB-4FS7/09HU153


Depth

304.8 mm | 12 in

Cable Length

153 m | 501.969 ft

Ordering Tree



Material Specifications

Finish	Powder coated
Material Type	Steel
Optical Specifications	
Fiber Mode	Singlemode

Environmental Specifications

Page 2 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 12, 2023



FPXB-4FS7/09HU153

Operating Temperature

Storage Temperature

-40 °C to +85 °C (-40 °F to +185 °F) -40 °C to +85 °C (-40 °F to +185 °F)

1

Packaging and Weights

Packaging quantity

Page 3 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 12, 2023

