LSX-67/0PD023



LSX Fiber Term Panel 4 Ru, 72 - SC/UPC, Singlemode I/O Ribbon, 23 Meters, Far end connection Stub

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with indoor/outdoor cable

Product Series LSX

General Specifications

Functionality Patching

Application Used in LSX-style frames only

Cable Exit Location Upward

Cable Stub TypeIndoor/outdoor, ribbon

ColorPutty whiteGrowth ConfigurationFully loaded

Interface, frontSC/UPCInterface, rearStub tail

Rack Type EIA 19 in | EIA 23 in

Rack Units 4

Shelf Movement Fixed

Total Ports, quantity 72

Dimensions

 Height
 177.8 mm | 7 in

 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in

 Cable Length
 23 m | 75.459 ft

Material Specifications

Finish Powder coated

Page 1 of 2



LSX-67/0PD023

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

