# LSX-67/0PD061



LSX Fiber Term Panel 4 Ru, 72 - SC/UPC, Singlemode I/O Ribbon, 61 Meters, Far end connection Stub

### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber patch panel, with indoor/outdoor cable

Product Series LSX

### General Specifications

**Functionality** Patching

**Application** Used in LSX-style frames only

Cable Exit Location Upward

Cable Stub TypeIndoor/outdoor, ribbon

ColorPutty whiteGrowth ConfigurationFully loaded

Interface, frontSC/UPCInterface, rearStub tail

Rack Type EIA 19 in | EIA 23 in

Rack Units 4

Shelf Movement Fixed

Total Ports, quantity 72

#### Dimensions

 Height
 177.8 mm | 7 in

 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in

 Cable Length
 61 m | 200.131 ft

## Material Specifications

**Finish** Powder coated

Page 1 of 2



# LSX-67/0PD061

Material Type Steel

**Optical Specifications** 

**Fiber Mode** Singlemode

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

