LSX-77/0T6031



LSX Fiber Termination Chassis 4 RU, 96 - SC/UPC, Singlemode OSP Stranded, 31 Meters, Far end connection Stub

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch chassis, with OSP cable

Product Series LSX

General Specifications

Functionality Patching

Application Used in LSX-style frames only

Cable Exit Location Upward

Cable Stub Type OSP, stranded

Color Putty white

Growth Configuration Fully loaded

Interface, front SC/UPC

Interface, rear Stub tail

Rack Type EIA 19 in | EIA 23 in

Rack Units 4

Shelf Movement Fixed

Total Ports, quantity 96

Dimensions

 Height
 177.8 mm | 7 in

 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in

 Cable Length
 31 m | 101.706 ft

Page 1 of 2



LSX-77/0T6031

Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

