# LSX-T7/OLH092



LSX Fiber Term Panel 6 Ru, 144 - SC/UPC, Singlemode IFC Ribbon, 92 Meters, Far end connection Stub

## Product Classification

Regional Availability	Latin America   North America
Portfolio	CommScope®
Product Type	Fiber patch panel, with IFC cable
Product Series	LGX

#### **General Specifications**

Functionality	Patching
Application	Used in LSX-style frames only
Cable Exit Location	Upward
Cable Stub Type	IFC, ribbon
Color	Putty white
Color, front	White
Growth Configuration	Fully loaded
Interface, front	SC/UPC
Interface, rear	Stub tail
Rack Type	EIA 19 in   EIA 23 in
Rack Units	6
Shelf Movement	Fixed
Total Ports, quantity	144
Dimensions	
Height	228.6 mm   9 in
Width	482.6 mm   19 in
Depth	304.8 mm   12 in

 Cable Length
 92 m
 301.837 ft

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 20, 2024



## LSX-T7/0LH092

#### Material Specifications

Finish Powder coated

Material Type

Steel

### **Optical Specifications**

Fiber Mode

Singlemode

### Packaging and Weights

Packaging quantity

### Regulatory Compliance/Certifications

1

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 20, 2024

