## 760242717

NG4-FLXACCSMCMP Cables with a maximum diameter of 10 mm (0.4") to 30 mm (1.2"), Kit of 6

**Product Classification** 

Regional Availability Asia | EMEA | Latin America | North America

**Product Type** Fiber cable clamp

General Specifications

**Application** Accepts cables with a maximum outer diameter of 10 to 30 mm (0.4 to 1.2 in)

**Environmental Specifications** 

Environmental Space Indoor

Packaging and Weights

Packaging quantity 6

Packaging Type Bag | Carton