

# FE-14126-R47

---



Fiber and power cable connection enclosure. Manages one 4-core or 8-core power trunk 12 AWG up to 6 AWG, one 24 fiber trunk cable and up to 7 hybrid tails. Internal trunk grounding. IP67

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Outdoor junction box

## General Specifications

<b>Color</b>	Gray
<b>Mounting</b>	Pipe, 76.2 mm (3 in) OD   Wall

## Dimensions

<b>Height</b>	304.8 mm   12 in
<b>Width</b>	355.6 mm   14 in
<b>Depth</b>	152.4 mm   6 in

## Material Specifications

<b>Material Type</b>	High-impact polycarbonate, UV resistant
----------------------	---

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +75 °C (-40 °F to +167 °F)
<b>Environmental Space</b>	Indoor   Outdoor

## Packaging and Weights

<b>Included</b>	Mounting kit
<b>Weight, net</b>	1.996 kg   4.4 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
---------------	-----------------------

# FE-14126-R47

---

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

